

THE JDM CT SPLIT- WITHOUT COOLING IN THE TECHNICS BOX EXTREMELY SMALL MEASUREMENTS!

- 4/6 drink selection buttons + chilled water
+ CO₂ water - OPTIONAL
- Bag-in-Box concentrates are stored in existing
furniture/base cabinet .
- Very small dimensions: Technics box 410x140x210mm
- Preselection CO₂ – OPTIONAL (model CO₂)
- 1 central drink exit with LED lighting (hygienic tempered
glass tube)
- Automatic cleaning and increased hygiene through
airtight seal of concentrates
- Fully electronic control of concentrate dosage and
output quantities
- Reliable and durable – premium materials,
robust surface
- Easy to use – easy refilling, programming,
service and cleaning
- Perfect mixing result through patented
MidMix®-system
- Multilingual LCD-Info Display
- Preparation for payment systems + accounting
- Carafe switch for quick serving by service staff
- Design of the drink dispense tower– OPTIONAL
- Base cabinet – OPTIONAL
- External cooling – OPTIONAL



JDM CT-S
Design



ESI (Easy
slide in)
labels

Technics box
without cooling
with extremely-small
dimensions
(4-6 flavours)



Available in the following versions:

JDM CT SPLIT L-4/6 STILL, JDM CT SPLIT L-4/6 CO₂,

DATA	JDM CT-SPLIT S-4 STILL	JDM CT-SPLIT S-4 CO ₂	JDM CT-SPLIT S-6 STILL	JDM CT-SPLIT S-6 CO ₂
Price in € excl. VAT				
Art. Nr.	fruc0501ok	fruc0506ok	fruc0511ok	fruc0516ok
Control-/Dispensing unit with tower	S 4	S 4	S 6	S 6
Width	210 mm	210 mm	210 mm	210 mm
Height	425 mm	425 mm	425 mm	425 mm
Depth	200 mm	200 mm	200 mm	200 mm
Exit height	max 190 mm	max 190 mm	max 190 mm	max 190 mm
Weight	5 kg	5 kg	5 kg	5 kg
Product selection buttons (incl. water)	5	6	7	8
Automatic carafe preselection (Extra)	✓	✓	✓	✓
ESI product labels ²	✓	✓	✓	✓
Mixing ratio concentrates	1+4 ... 1+49	1+4 ... 1+49	1+4 ... 1+49	1+4 ... 1+49
Concentrates in machine	-	-	-	-
Dosage of product selection	150-500ml / PULS	150-500ml / PULS	150-500ml / PULS	150-500ml / PULS
Dosage of preselection EXTRA/jug	max 2000ml	max 2000ml	max 2000ml	max 2000ml
Technics box	Split	Split	Split (modular)	Split (modular)
Width	410 mm	410 mm	595 mm h=140 mm	595 mm h=140 mm
Height	140 mm	140 mm	270 mm b=410 mm	270 mm b=410 mm
Depth	210 mm	210 mm	210 mm	210 mm
Weight	max. 10 kg	max. 10 kg	max. 12 kg	max. 12 kg
Distance technics box/ dispensing unit vertical	max. 1,5 m	max. 1,5 m	max. 1,5 m	max. 1,5 m
Distance technics box/ dispensing unit	max. 5,0 m	max. 5,0 m	max. 5,0 m	max. 5,0 m
Distance concentrate/ technics box vertical	max. 1,5 m	max. 1,5 m	max. 1,5 m	max. 1,5 m
Distance concentrate/ technics box	max. 5,0 m	max. 5,0 m	max. 5,0 m	max. 5,0 m
Cooling capacity	extern	extern	extern	extern
Dispensing temperature	extern	extern	extern	extern
Water pressure in bar	min 1,5 bar/max 6 bar	min 1,5 bar/max 6 bar	min 1,5 bar/max 6 bar	min 1,5 bar/max 6 bar
Voltage	230 V/ 50 Hz	230 V/ 50 Hz	230 V/ 50 Hz	230 V/ 50 Hz
Power max.	extern	extern	extern	extern
with CO ₂ -carbonator	extern	extern	extern	extern
FSS ¹	✓	✓	✓	✓
Flowmeter (water)	✓	✓	✓	✓
Dispense tower glass LED backlight	OPTIONAL	-	OPTIONAL	-
Dispensing area LED light	✓	✓	✓	✓
Coin validator/cashless	OPTIONAL	OPTIONAL	OPTIONAL	OPTIONAL
Bookkeeping	✓	✓	✓	✓
Payment systems	parallel / EXE	parallel / EXE	parallel / EXE	parallel / EXE
Syrup Injection Valve (SIV ³)	✓	✓	✓	✓
Water gallon + pumpset	OPTIONAL	OPTIONAL	OPTIONAL	OPTIONAL
Control of Disinfection and Sanitation intervals	✓	✓	✓	✓

ALL our models are equipped with the unique and patented mixing system MidMix II.

1) FSS = Flood security system: avoids water flood problems due to extra safety valve on water entrance.

2) ESI = easy slide in: for fast and easy change of product labels

3) SIV = syrup injection valve for perfect mixing result

SIZE INCL. PACKAGING	JDM CT-SPLIT S-4 STILL	JDM CT-SPLIT S-4 CO ₂	JDM CT-SPLIT S-6 STILL	JDM CT-SPLIT S-6 CO ₂
Width	570 mm	570 mm	570 mm	570 mm
Height	465 mm	465 mm	465 mm	465 mm
Depth	470 mm	470 mm	470 mm	470 mm
Weight incl. Packaging	18 kg	18 kg	20 kg	20 kg
MACHINE PACKAGE/PALLET				
Euro pallet 80 x 120 cm	8	8	8	8
UK-size pallet 100 x 120 cm	12	12	12	12

